

1

2



3

4

Tolerance class

Nr.	Name	Material
1	Body	PE
2	Service well	PE, D500
3	Telescopic cover	GRAF
4	Inlet pipe	PE, D160
5	Outlet pipe D63	PE
6	Elbow	Brass, DN50
7	Discharge pipe	PE, D63
8	Pump DAB FEKA 550	
9	Cable bushing	
10	Coupling	Brass, D63- 2"
11	Check valve	DN50
12	Ball valve	Brass, DN50
13	Elbow	Brass, 2"vk
14	Seal	
15	Camlock coupling	2"; PP

1. To lift the pump out you must unscrew the Camlock coupling (pos.15) and then you can lift the pump out.



10.09.2021

Date

Engr.

Signature

Sheets

Pumping station "Edgar"

42682

Rv

eccua

Mass

Number

All rights reserved.

Z:\Eccua\Pumplad\Va\ikepump\lad\T\ellimused\42682 Edgar, 1,5m, Plastl, DAB Feka 550 (Camlock) DN50 sisu\42682 Edgar, 1,5m, Plastl, DAB Feka 550 (Camlock) DN50 sisu.dft